



### Configuration FACS Aria (1/3)

Laser	Filtre		Fluorochromes	λ Emission
	BP	LP		
Violet 405nm	450/40		Cascade Blue	419
			DyLight 405	420
			Alexa Fluor 405	421
			VioBlue	455
			Pacific Blue	450
			Alexa Fluor 405	405
			BV421	422
			V450	450
			eFluor450	450
			DAPI	461
			Hoechst 33342	461
			CFP	475
			BV480	478
			510/50	502
	Pacific Green	500		
	eFluor 506	506		
	V500	500		
	BV510	510		
	VloGreen	520		
	560/40	545	Qdot565	565
			Pacific Orange	550
	585/42	555	Qdot 585	585
			BV605	605
			Super Bright 600	600
	670/30	635	Qdot655	655
			BV650	650
			SuperBright 645	645
	710/50	685	Qdot 705	705
SuperBright 702			702	
BV711			711	
BV785			785	

**Configuration FACS Aria (2/3)**

Laser	Filtre		Fluorochromes	λ Emission
	BP	LP		
<b>Bleu 488nm</b>	530/30	502	FITC Alexa 488 GFP Cy3 YFP BB515	519 520 510 560 527 515
	695/40	655	BB700 PerCP PerCP-Cy5.5 PerCP-eFluor710 PerCP-Vio700 PerCP-eFluor 710	700 678 676 710 700 710

Laser	Filtre		Fluorochromes	λ Emission
	BP	LP		
<b>Jaune-Vert 561nm</b>	582/15		Cy3 dTomato RFP PE DesRed	566 581 588 575 585
	610/20	600	IP PE-Texas Red mCherry PE-Alexa 610 PE-eFluor 610 PE-Vio615 eFluor 615 PE-CF 594 / Alexa 594	620 616 610 610 610 615 615 594
	670/14	630	7AAD PE-Cy5 Alexa 668 PE-Alexa 680	647 670 668 680
	710/50	685	PE-Cy5.5 PE-Alexa 700 PE-Vio700	675 700 700
	780/60	735	PE-Alexa750 PE-Vio770 PE-Cy7	750 770 778

**Configuration FACS Aria (3/3)**

Laser	Filtre		Fluorochromes	λ Emission
	BP	LP		
<b>Rouge 635nm</b>	660/20		APC	660
			Cy5	666
			eFluor660	660
			Alexa 647	647
			DyLight 650	650
	730/45	690	Alexa 700	695
			Alexa 680	702
			APC-R700	700
			Cy5.5	716
			APC-Cy5.5	716
	780/60	735	APC-Alexa750	774
			APC-Cy7	785
			APC-H7	785
			APC-Vio770	770
			APC-eFluor780	780
APC/Fire 750			750	